

# Endo Reciprocation

|                            | Wave-One   | EndoEZE   | Tango         | Reciproc   |
|----------------------------|--|---|---------------|--|
| Manufacturer               | Tulsa (Dentsply)   | Ultradent   | EDS           | VDW  |
| Intro Kit Price            | \$2,078.30   | \$1,228.99  | \$630.00      | \$1,220  |
| Motor                      | Included   | Included  | NA            | Included   |
| Recommended Handpiece      | Included   | Included  | Included      | Included   |
| TOTAL Into Cost            | 2078.3   | 1228.99   | \$630         | \$191  |
| Refill Price (Avg)         | \$56   | 39.99   | \$79.75       | 89   |
| Files per refill kit       | 3  | 5   | 6             | 6  |
| # of Uses Per File         | 1  | 1   | 3             | 1  |
| Avg. Cost Per File         | \$18.67  | \$8.00  | \$4.43        | \$14.83  |
| # of File Sizes for System | 3  | 14  | 2             | 1  |
| Direct/Dealer              | Direct   | Direct  | Dealer        |  |
| Rotary / Reciprocating     | Reciprocating  | Reciprocating   | Reciprocating | Reciprocating  |
| Files                      | Small 21/06<br>Medium 25/08<br>Large 40/08                     | 3 Files (1,2,3) Approximate Taper: Shaping 1 = 2.5%, Shaping C = 3.5%, Shaping 2 = 4.5%, Shaping 3 = 6%<br>Tip Diameter:<br>Shaping 1 = .10mm<br>All others = .13mm   |               | <b>Just one of the three files needs to be used, depending on the canal.</b><br><b>R25</b> prepares the root canal to a diameter of 0.25 mm with a taper of .08 over the first apical millimetres.<br><b>R40</b> prepares the root canal to a diameter of 0.40 mm with a taper of .06 over the first apical millimetres.<br><b>R50</b> prepares the root canal to a diameter of 0.50 mm with a taper of .05 over the first apical millimetres. |
| Obturers & GP Points       | Wave-One Obturators. Gutta Purcha Comes in Small Med and Large | Endo Rez Obturation.<br>Resin-Coated Gutta Percha Points<br>The ONLY resin-coated gutta percha<br>Resin coating bonds chemically to EndoREZ<br>Creates a true monoblock in the canal space<br>Compatible and bonds with resin-based sealers |               |  |